

Seip Infopost

NEW MIDI-HANDSET SKR433-3



We are pleased to introduce to the market our new Midi Handset SKR344-3, which will be supplied with all our operators as standard. The attractive, sleek design incorporates a solid steel frame giving durability, coupled with the appearance and feel of this quality product. The size of our new Handset is smaller than the oval Handset, with a total weight of just 24 g. Despite this, the range is outstanding – up to 100 metres!



A perfect team: Comparison of the new MIDI and the MINI handset

A pleasing appearance and functionality

Despite the smaller size of our new Handset, the buttons are precise and easy to use. As the buttons are set below the main body of the Handset, this makes unintended operation quite difficult. A LED light is clearly visible when a button is pressed to open and close the garage door. When operators are shipped out with the new handsets included, we will be supplying as standard a handset holder, together with screw fixings.

Compatibility

The new SKR433-3 is fully compatible with previous SKR transmitters. Therefore it can be used as a replacement for any TS and TM series Operators and with our external receivers.



Real Steel to hold the Key-Ring

The solid steel frame produces a sturdy key ring holder.



Seip Infopost

The perfect partner for the SKR433-3 : Handset Holder for Wall Mounting



The handset holder is fitted to the wall with the screws provided. It provides a solid and secure home for an additional handset and/or doubles up as a Wall Mounted Remote. It is also possible to leave some keys attached to the Handset.



HINT!

When using the handset with the TM series Operator, the integrated light on the Operator can be switched on without putting the Operator in to action. Simply press button numbers 3 and 4 simultaneously. The light will go off automatically once the set lighting time has elapsed. This works just the same as the previous SKR433-1 oval Handset.

One simple slide to have a wall-remote

One difference to the previous versions: hassle free, with a perfect and stable fit every time!



At a glance: Changing the battery



The battery holder can easily be accessed by removing the battery lid. The CR2032 battery used for the SKR433-3 is widely available and simple to exchange. Using a little screw driver will make it easier to remove the battery.

Availability of the previous handset SKR433-1

The predecessor SKR433-1 was widely liked for its' big round button. Therefore we will keep a small stock of the oval MIDI's. However, once greater quantities should be required a delivery time of 2 to 3 weeks may apply.



11, Monument Business Park
OX44 7RW, Chalgrove, Oxford
Tel 01865-400 469
Fax 01865-400 217
E-Mail info@seip.co.uk
www.seip.co.uk